

Ionpure® MX Low Flow Continuous Electrodeionization(CEDI) Modules

Ionpure® MX Module – Low Flow



The Ionpure® MX modules are designed with proven continuous electrodeionization (CEDI) technology. Performance on these modules has been optimized to produce high purity water for laboratory and smaller scale applications. A wide nominal flow range from 30 – 500 liters per hour increases the applicability for single module installations.

Ionpure® modules consistently deliver maximum reliability and superior performance for power, HPI/CPI, microelectronics, food and beverage and laboratory applications without regeneration downtime



MX Series Features

- Double O-ring seal guarantees leak-free operation
- Superior electrical isolation
- 75 psi (5 bar), 113°F (45°C) continuous operation
- Proprietary “all filled” concentrating compartments eliminate recirculation pump and brine injection
- Significantly lower operating costs than conventional ion exchange
- Generates mixed bed deionized water without the use of chemicals
- No need for acid/caustic, neutralization systems or DI tank exchanges
- Consistent continuous production instead of batch cycle variability



For additional information call +31 165 348 253 or visit our website at www.purewatergroup.com



Engineering purity

INTERNATIONAL IONPURE MASTER SERVICE PROVIDER

Ionpure® MX Low Flow Continuous Electrodeionization (CEDI) Modules

Electrical requirements

Maximum module requirements are 27, 53, 106, 213, 426 VDC, 2.5 Amps.

Operating environment

Installation should be indoors with no direct sunlight and it should have a maximum ambient temperature of 113°F (45°C).

Quality Assurance Standards

CE marked. Each module is factory tested to meet strict industry standards and is manufactured in an ISO 9001 and ISO 14000 quality and environmental management system.

Maximum Feed Water Specifications	
Feed water conductivity equivalent, Including CO ₂ and Silica	< 40 µS/cm
Feed water source	RO permeate
Temperature	40 - 113°F (5 - 45°C)
Inlet pressure	20 - 75 psi (1.4 - 5 bar)
Maximum total chlorine (as Cl ₂)	< 0.02 ppm
Iron (Fe)	< 0.01 ppm
Manganese (Mn)	< 0.01 ppm
Sulphide (S ⁻)	< 0.01 ppm
pH	4 - 11
Total hardness (as CaCO ₃)	< 1.0 ppm
Dissolved organics (TOC as C)	< 0.5 ppm
Silica (SiO ₂)	< 1.0 ppm

Typical Module Performance

Physical Specifications		
Dimensions		
Item Number	L	H
MX30	7.25" (18.41 cm)	7.0" (17.78 cm)
MX60	8.83" (21.27 cm)	7.0" (17.78 cm)
MX125	10.77" (27.37 cm)	7.0" (17.78 cm)
MX250	15.45" (39.23 cm)	7.0" (17.78 cm)
MX500	24.79" (62.90 cm)	7.0" (17.78 cm)

Operating Parameters	
Recovery	90 - 95%
Maximum Feed Pressure	75 psi (5 bar)
Pressure Drop Range at Nominal Flow	10 - 20 psi (0.7 - 1.4 bar)
Maximum Feed Temperature	113°F (45°C)
Product Water Quality	
Product resistivity	> 16 MΩ-cm*
Silica (SiO ₂) removal	90 - 99% depending on feed conditions

*Actual performance may be determined using the IP-Pro projection software available from Ionpure.

Flow and Physical Specifications					
Model Number	Product Flow min. gpm (l/h)	Product Flow nominal gpm (l/h)	Product Flow max. gpm (l/h)	Shipping Weight lbs (kg)	Operating weight lbs (kg)
MX30	0.06 (15)	0.13 (30)	0.19 (45)	12 (4.5)	10 (5.4)
MX60	0.13 (30)	0.26 (60)	0.39 (90)	16 (5.9)	13 (6.8)
MX125	0.27 (62.5)	0.55 (125)	0.825 (187)	21 (9.55)	23 (10.45)
MX250	0.55 (125)	1.1 (250)	1.65 (375)	28 (12.73)	31 (14.09)
MX500	1.1 (250)	2.2 (500)	3.3 (750)	43 (19.55)	47 (21.36)

Pure Water Group

Korte Hei 3
4714 RD Sprundel
Tel. +31 165 348 253
Fax +31 165 348 254
info@purewatergroup.com

Ionpure and Flexmount are trademarks of Evoqua, its subsidiaries or affiliates.

The information provided in this literature contains merely general descriptions or characteristics of performance which in actual case of use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in terms and of the contract